

FD3-MP864J00000FOC



IFDH 3000 Indoor Fiber Distribution Hub, 864 fiber, SC/APC, ribbon pigtails, splice cabinet

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	IFDH 3000

General Specifications

Functionality	Patching Splicing
Access	Front
Adapters, quantity	864
Cable Type	Pigtails - Ribbon
Color	Putty white
Fibers per Feeder Cable, quantity	48
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Rack
Port, quantity	864
Splitter Slots, quantity	22

Dimensions

Height	1,831.59 mm 72.11 in
Width	657.35 mm 25.88 in
Depth	426.47 mm 16.79 in
Enclosure Size	Large

Material Specifications

Finish	Powder coated
Material Type	Aluminum

FD3-MP864J00000FOC

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications

Environmental Space Indoor

Packaging and Weights

Packaging quantity 1