760257108 | BUDI-FM-TS236-US00



BUDI™ Fiber Optic Wall Mount Enclosure for Splice/Patch, 36 SC/APC adapters

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Wall box
Product Brand	BUDI™
Product Series	BUDI-FM
Country Specific for	United States
Warranty	For more information, please consult our Product Warranty guidelines

General Specifications

Functionality	Patching Splicing
Adapter Ports, quantity	36
Adapters, quantity	36
Color	Gray
Interface	SC/APC
Mounting	Wall mount
Patching Capacity, maximum	36
Pigtails Included, quantity	36
Dimensions	
Height	480 mm 18.898 in
Height, with cover	550 mm 21.654 in
Width	360 mm 14.173 in
Depth	175 mm 6.89 in
Material Specifications	

Material Type

PC/ABS

Page 1 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 31, 2024



760257108 | BUDI-FM-TS236-US00

Environmental Specifications

Environmental Space	Indoor/Outdoor
Flammability Rating	UL 94 V-0
UV Resistance	UV stabilized

Packaging and Weights

Packaging quantity	1
Packaging Type	Carton

Regulatory Compliance/Certifications

Agency

ROHS

CHINA-ROHS

Classification

Above maximum concentration value Compliant/Exempted Compliant/Exempted



* Footnotes

Warranty

For more information, please consult our Product Warranty guidelines

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: July 31, 2024

