

# 760258039 | HCA-ACC-3mm SC/APC Test Lead 50FT, 2x Cvtr



HCA-ACC-3mm SC/APC Test Lead 50FT, Full size and DLX converter included

- Prodigy converters simplify installation and maintenance by reducing splicing requirements in the distribution portion of the network

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber test patch cord
<b>Product Brand</b>	PRODIGY™
<b>Product Series</b>	HCA

## General Specifications

<b>Color, boot A</b>	Black
<b>Color, connector A</b>	Black
<b>Color, connector B</b>	Green
<b>Interface, Connector A</b>	Prodigy
<b>Interface, Connector B</b>	SC/APC
<b>Jacket Color</b>	Yellow

## Dimensions

<b>Cable Assembly Length</b>	15.24 m   50 ft
------------------------------	-----------------

## Mechanical Specifications

<b>Dust Cap Pulling Force, minimum</b>	445 N   100.04 lbf
--	--------------------

## Optical Specifications

<b>Insertion Loss, maximum</b>	0.3 dB
<b>Insertion Loss, typical</b>	0.15 dB
<b>Return Loss, minimum</b>	65 dB

## Environmental Specifications

<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
------------------------------	--------------------------------------

# 760258039 | HCA-ACC-3mm SC/APC Test Lead 50FT, 2x Cvtr

---

<b>Storage Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Environmental Space</b>	Indoor/Outdoor
<b>Qualification Standards</b>	IEC 60793   IEC 60794