XPPCSRJ/J

Base Product



CommScope XPND™ Singlemode SC/APC to SC/APC, Fiber Patch Cord, 1.6 mm Simplex, Dual Rated LSZH/Riser

Product Classification

Regional Availability

Latin America | North America

Portfolio CommScope®

Product Type Fiber patch cord, simplex

Product Brand SYSTIMAX InstaPATCH® 360

Product Series XPPC

General Specifications

Connector A, quantity

Color, boot A Green
Color, connector A Green

Connector B, quantity 1

Color, boot B Green
Color, connector B Green
Interface, Connector A SC/APC
Interface, Connector B SC/APC
Jacket Color Yellow

Total Fibers, quantity 1

Dimensions

Polarity

Cable Assembly Length Range (m) 1 - 999


Diameter Over Jacket 1.6 mm | 0.063 in

Ordering Tree



Method B

XPPCSRJ/J



Mechanical Specifications

Cable Retention Strength, maximum 11.24 lb @ 0 ° | 4.40 lb @ 90 °

Optical Specifications

Fiber Mode Singlemode

Fiber Type G.652.D | G.657.A1, TeraSPEED®

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \text{ (+14 }^{\circ}\text{F to } +140 \,^{\circ}\text{F)}$

Operating Temperature, pending approval $-20 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-4 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Environmental Space Dual Rated LSZH/Riser

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



Included Products

460125784 - TeraSPEED® SC APC Connector for 1.6 mm Fiber, Duplex, Singlemode, green

760164160 – Fiber Indoor Cable, OptiSPEED® 1.6mm Low Smoke Zero Halogen Riser, 1-fiber Simplex,

N-001-SP-8W-F16YL/E Singlemode G.652.D and G.657.A1, Yellow jacket color, Eca Flame Rating

COMMSCOPE®