


# XPPCSR/M

Base Product



CommScope XPND™ Singlemode LC/APC to LC/APC, Fiber Patch Cord, 1.6 mm Simplex, Dual Rated LSZH/Riser

## Product Classification

Regional Availability	Latin America   North America
Portfolio	CommScope®
Product Type	Fiber patch cord, simplex
Product Brand	SYSTIMAX InstaPATCH® 360
Product Series	XPPC

## General Specifications


Connector A, quantity	1
Color, boot A	Green
Color, connector A	Green
Connector B, quantity	1
Color, boot B	Green
Color, connector B	Green
Interface, Connector A	LC/APC
Interface, Connector B	LC/APC
Jacket Color	Yellow
Polarity	Method B
Total Fibers, quantity	1

## Dimensions

Cable Assembly Length Range (m)	1 – 999
Diameter Over Jacket	1.6 mm   0.063 in

## Ordering Tree

# XPPCSR/M



## Mechanical Specifications

**Cable Retention Strength, maximum** 11.24 lb @ 0 ° | 4.40 lb @ 90 °

## Optical Specifications

**Fiber Mode** Singlemode  
**Fiber Type** G.652.D | G.657.A1, TeraSPEED®

## Environmental Specifications

**Operating Temperature** -10 °C to +60 °C (+14 °F to +140 °F)  
**Operating Temperature, pending approval** -20 °C to +70 °C (-4 °F to +158 °F)  
**Environmental Space** Dual Rated LSZH/Riser

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## Included Products

- |                                  |  |
|----------------------------------|--|
| 760164160<br>N-001-SP-8W-F16YL/E | – Fiber Indoor Cable, OptiSPEED® 1.6mm Low Smoke Zero Halogen Riser, 1-fiber Simplex, Singlemode G.652.D and G.657.A1, Yellow jacket color, Eca Flame Rating |
| 860637444                        | – TeraSPEED® LC/APC Connector for 1.6 mm Fiber, Singlemode, Green, Short Boot  |