

# F062HKS2

---



FlexTwist® Flexible Twist for WR62, 12.4–18.0 GHz, with interface types PDR140 and PBR140, 600 mm

## Product Classification

<b>Product Type</b>	Rectangular waveguide, flexible twist
<b>Product Brand</b>	FlexTwist®

## General Specifications

<b>Component</b>	Flexible Twist
<b>Interface</b>	PDR140
<b>Interface 2</b>	PBR140

## Dimensions

<b>Length</b>	600 mm   23.622 in
<b>Waveguide Size</b>	WR62   WG18   R140

## Electrical Specifications

<b>Attenuation</b>	0.99 dB/m   0.302 dB/ft
<b>Average Power</b>	400 W
<b>Operating Frequency Band</b>	12.4 – 18.0 GHz
<b>Peak Power</b>	100 kW
<b>VSWR</b>	1.1

## Mechanical Specifications

<b>Minimum Bend Radius, Multiple Bends (E Plane)</b>	52 mm   2.047 in
<b>Minimum Bend Radius, Multiple Bends (H Plane)</b>	102 mm   4.016 in
<b>Maximum Twist</b>	445 °/m   135.636 °/ft
<b>Pressurization, maximum</b>	0.31 N/mm <sup>2</sup>   45 psi

# F062HKS2

---

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system