Copper Cable, category 5e, 4 pair, UTP, CM rated, 24 AWG, 100 m, gray



Product Classification

Regional Availability Asia

Portfolio NETCONNECT®

Product Type Twisted pair cable

General Specifications

ANSI/TIA Category 5e

Cable Component Type Horizontal

Cable Type U/UTP (unshielded)

Conductor Type, singles Solid
Conductors, quantity 8

Jacket Color Gray

Pairs, quantity 4

Transmission Standards ANSI/TIA-568.2-D | CENELEC EN 50288-6-1 | ISO/IEC 11801 Class E

Dimensions

 Cable Length
 100.002 m | 328.09 ft

 Diameter Over Jacket, nominal
 5.105 mm | 0.201 in

Conductor Gauge, singles 24 AWG

Electrical Specifications

Operating Voltage, maximum 80 V

Remote Powering Fully complies with the recommendations set forth by IEEE 802.3bt (Type 4) for the safe delivery

of power over LAN cable when installed according to ISO/IEC 14763-2, CENELEC EN 50174-1,

CENELEC EN 50174-2 or TIA TSB-184-A

Material Specifications

Page 1 of 2



6-1859632-4

Conductor MaterialBare copperInsulation MaterialPolyolefinJacket MaterialPVC

Environmental Specifications

Operating Temperature $-20 \,^{\circ}\text{C} \text{ to } +60 \,^{\circ}\text{C} \, (-4 \,^{\circ}\text{F to } +140 \,^{\circ}\text{F})$

Packaging and Weights

Packaging Type Reelex

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant

