760238702 | IFDB-M-T-P04S2-NNN-0



IFDB Fiber Optic Wall Box with 4 SC/APC adapters, with pigtails

- Allows splicing those fibers from an indoor riser cable to the individual drops
- Allows fibers from certain riser cables to be broken out without interrupting the strength member
- Separate storage of un-connected fibers from spliced drop fibers
- Compatible with mechanical, SMOUV and ANT splice protectors
- In-line and butt configuration possible for main riser cable

Product Classification

Regional Availability EMEA

Product Type Fiber wall box

Product Series IFDB

General Specifications

Functionality Patching | Splitting

Adapters, quantity 4

ColorLight grayFront Cover TypeScrew-onInterfaceSC/APC

Mounting Floor | Wall

Dimensions

 Height
 216 mm | 8.504 in

 Width
 126 mm | 4.961 in

 Depth
 49 mm | 1.929 in

Material Specifications

Material Type Thermoplastic

Optical Specifications

Fiber Mode Singlemode

Environmental Specifications



760238702 | IFDB-M-T-P04S2-NNN-0

Environmental Space Indoor

Flammability Rating UL 94 V-0

Qualification Standards IEC 60529, IP30

Packaging and Weights

Included Fiber pigtail assemblies

Packaging quantity 12

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

