


CW1527-000 | FDC-W8-FAT-S1/8-10NN-1N-INT



FDC Fiber Optic Splice/Patch Closure, Gel Cable Sealing, 8 SC/UPC Adapters, 24 fusion splices

Product Classification

Regional Availability	Asia
Product Type	Single-ended, rectangular fiber closure
Product Series	FDC

General Specifications

Cable Ports Quantity, total	4 round ports + 8 round ports
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Color	Black
Mounting	Manhole Pedestal Strand Wall
Port Type	SC/UPC
Port, quantity	8
Splice Tray Included, quantity	1
Splice Tray Type Included	24-way, heat shrink
Splitter Type	No splitter
Splitter, quantity	0

Dimensions

Height	237 mm 9.331 in
Width	76.5 mm 3.012 in
Length	266 mm 10.472 in

Material Specifications

Material Type	Rugged polymer
----------------------	----------------

Environmental Specifications

Environmental Space Above ground | Below ground

Packaging and Weights

Packaging quantity 1

Packaging Type Box | Carton

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant

UK-ROHS

Compliant

