FMT-DST080A00-A12P



FMT Fiber Termination/Storage Panel, with sliding tray, 12 LC/UPC, singlemode, 1RU, 19 in, putty white

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch/storage panel

Product Series FMT

General Specifications

Functionality Patching

Body Style Symmetrical

Color Black

Color, front Putty white

Interface, front LC/UPC

Rack Type EIA 19 in | EIA 23 in

Rack Units 1

Shelf Movement Sliding

Total Ports, quantity 12

Dimensions

 Height
 44.45 mm | 1.75 in

 Width
 482.6 mm | 19 in


Depth 279.91 mm | 11.02 in

Cable Stub Length 0 m | 0 ft

Ordering Tree



FMT-DST080A00-A12P



Material Specifications

Finish Powder coated

Material Type Steel

Optical Specifications

Fiber Mode Singlemode

Packaging and Weights

Packaging quantity

I

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant



