

FMX-GSTOJOA00-T48V



FMT Fiber Termination Panel, with sliding tray, vented, 48 SC/APC, singlemode, 2RU, 19 in, putty white

Product Classification

| | |
|------------------------------|-------------------------------|
| Regional Availability | Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch/splice panel |
| Product Series | FMT |

General Specifications

| | |
|------------------------------|-----------------------|
| Functionality | Patching Splicing |
| Body Style | Symmetrical |
| Color | Black |
| Color, front | Putty white |
| Interface, front | SC/APC |
| Rack Type | EIA 19 in EIA 23 in |
| Rack Units | 2 |
| Shelf Movement | Sliding |
| Total Ports, quantity | 48 |

Dimensions

| | |
|---------------|----------------------|
| Height | 88.9 mm 3.5 in |
| Width | 482.6 mm 19 in |
| Depth | 279.91 mm 11.02 in |

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

FMX-GSTOJOA00-T48V

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

