

# FSB-SGJ27200C00000

---

FSB Fiber Splitter Box, outdoor, SC/APC, 72 ports, heat shrink splice tray, 3 splitter slots, putty white

## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Fiber wall box
<b>Product Series</b>	FSB

## General Specifications

<b>Functionality</b>	Patching   Splicing   Splitting
<b>Access</b>	Front
<b>Cable Color</b>	White
<b>Cable Type</b>	Pigtails - Stranded
<b>Enclosure Color</b>	Putty white
<b>Interface</b>	SC/APC
<b>Lock Type</b>	Padlock ready
<b>Mounting</b>	Wall
<b>Port Capacity, maximum</b>	72
<b>Port, quantity</b>	72

## Dimensions

<b>Height</b>	330.2 mm   13 in
<b>Width</b>	482.6 mm   19 in
<b>Depth</b>	254 mm   10 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Environmental Space</b>	Outdoor
<b>Qualification Standards</b>	NEMA, Type 4

## Packaging and Weights

# FSB-SGJ27200C00000

---

**Packaging quantity** 1  
**Packaging Type** Box | Carton

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

