

MX6-FMB70LVF0030

OMX Fiber Termination Block with IFC cable, 96 SC/UPC, singlemode, putty white, left, 30 meters, Stub tail at far end

OBSOLETE

This product was discontinued on: December 30, 2018

Product Classification

| | |
|------------------------------|--------------------------------------|
| Regional Availability | EMEA Latin America North America |
| Product Type | Fiber patch block, with IFC cable |
| Product Brand | OMX600® |
| Product Series | OMX |

General Specifications

| | |
|------------------------------|-------------------------------|
| Functionality | Patching |
| Application | Used in OMX-style frames only |
| Body Style | Left orientation |
| Cable Exit Location | Upward |
| Cable Type | IFC - Stranded |
| Color | Putty white |
| Color, front | Putty white |
| Growth Configuration | Fully loaded |
| Interface, front | SC/UPC |
| Interface, rear | Stub tail |
| Rack Type | OMX |
| Shelf Movement | Hinged |
| Total Ports, quantity | 96 |

Dimensions

| | |
|---------------------|-----------------------|
| Height | 373.126 mm 14.69 in |
| Width | 203.2 mm 8 in |
| Depth | 283.21 mm 11.15 in |
| Cable Length | 30 |

MX6-FMB70LVF0030

Material Specifications

| | |
|----------------------|---------------|
| Finish | Powder coated |
| Material Type | Steel |

Optical Specifications

| | |
|-------------------|------------|
| Fiber Mode | Singlemode |
|-------------------|------------|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| REACH-SVHC | Compliant as per SVHC revision on www.commscope.com/ProductCompliance |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

