

# MX6-PMD4L1120

---

OMX Fiber Termination Block, pre-terminated with pigtails, 144 ST/UPC, singlemode, putty white, left oriented

**OBSOLETE**

This product was discontinued on: December 30, 2018

## Product Classification

|                              |                                      |
|------------------------------|--------------------------------------|
| <b>Regional Availability</b> | EMEA   Latin America   North America |
| <b>Product Type</b>          | Fiber patch block                    |
| <b>Product Brand</b>         | OMX600®                              |
| <b>Product Series</b>        | OMX                                  |

## General Specifications

|                              |                               |
|------------------------------|-------------------------------|
| <b>Functionality</b>         | Patching                      |
| <b>Application</b>           | Used in OMX-style frames only |
| <b>Body Style</b>            | Left orientation              |
| <b>Color</b>                 | Putty white                   |
| <b>Color, front</b>          | Putty white                   |
| <b>Growth Configuration</b>  | Fully loaded                  |
| <b>Interface, front</b>      | ST/UPC                        |
| <b>Rack Type</b>             | OMX                           |
| <b>Shelf Movement</b>        | Hinged                        |
| <b>Total Ports, quantity</b> | 144                           |

## Dimensions

|               |                       |
|---------------|-----------------------|
| <b>Height</b> | 373.126 mm   14.69 in |
| <b>Width</b>  | 203.2 mm   8 in       |
| <b>Depth</b>  | 283.21 mm   11.15 in  |

## Material Specifications

|                      |               |
|----------------------|---------------|
| <b>Finish</b>        | Powder coated |
| <b>Material Type</b> | Steel         |

# MX6-PMD4L1120

---

## Optical Specifications

**Fiber Mode** Singlemode

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

| <b>Agency</b> | <b>Classification</b>  |
|---------------|--|
| CHINA-ROHS    | Above maximum concentration value  |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant/Exempted   |
| UK-ROHS       | Compliant/Exempted   |

