## PH3579-000 | FIST-GPST-12-QAN-N-PH



FIST GPST Fiber Termination/Splice Tray, 12/24 ports, no adapters, ANT splice chip, 19 in, gray, left patch cord routing

### **Product Classification**

Regional Availability EMEA

Product Type Fiber patch/splice tray

Product Brand FIST®

Product Series FIST-GPST

## General Specifications

Functionality Patching | Splicing

**Color** Gray

Interface, front Unloaded

Patch Cord Entry Location Front, left side

**Splicing Type** ANT, single fiber fusion

Total Ports, quantity 12

#### Dimensions

 Height
 18 mm | 0.709 in

 Width
 355 mm | 13.976 in

 Depth
 190 mm | 7.48 in

## **Optical Specifications**

**Fiber Mode** Singlemode

## **Environmental Specifications**

Operating Temperature  $-5 \,^{\circ}\text{C}$  to  $+45 \,^{\circ}\text{C}$  (+23  $^{\circ}\text{F}$  to +113  $^{\circ}\text{F}$ )

Storage Temperature  $-30 \,^{\circ}\text{C}$  to  $+60 \,^{\circ}\text{C}$  (-22  $^{\circ}\text{F}$  to +140  $^{\circ}\text{F}$ )

Page 1 of 2



# PH3579-000 | FIST-GPST-12-QAN-N-PH

**Relative Humidity** Up to 93%, non-condensing

Packaging and Weights

Packaging quantity 1

