PH3834-000 | FIST-GPST-12-AAN-N



FIST GPST Fiber Patch Tray, 12/24 ports, no adapters, 19 in, gray, left /right patch cord routing

Product Classification

Regional Availability	EMEA
Product Type	Fiber patch tray
Product Brand	FIST®
Product Series	FIST-GPST

General Specifications

Functionality	Patching
Color	Gray
Interface, front	Unloaded
Patch Cord Entry Location	Front, left side Front, right side
Patching Capacity, maximum	12
Splicing Capacity, maximum	0
Total Ports, quantity	12

Dimensions

Height	18 mm 0.709 in
Width	355 mm 13.976 in
Depth	190 mm 7.48 in

Optical Specifications

Fiber Mode

Singlemode

Environmental Specifications

Operating Temperature

-5 °C to +45 °C (+23 °F to +113 °F)

Page 1 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: October 5, 2022



PH3834-000 | FIST-GPST-12-AAN-N

Storage Temperature

-30 °C to +60 °C (-22 °F to +140 °F)

Relative Humidity

Up to 93%, non-condensing

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

1

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

Page 2 of 2

©2022 CommScope, Inc. All rights reserved. All trademarks identified by ® or [™] are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: October 5, 2022

