


RDT-SJ12J2PC50020

RapidFiber® FDT Distribution Terminal, 12-fiber, SC/APC, 500 ft



Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber distribution terminal
Product Brand	RapidFiber®
Product Series	FDT

General Specifications

Adapters, quantity	12
Cable Color	Yellow
Cable Entry Location	Bottom left Top left Top right
Cable Type	Indoor/outdoor - Stranded
Color	Putty white
Front Cover Type	Hinged with lock
Growth Configuration	Fully loaded
Interface	SC/APC
Interface, stub	No connector
Mounting	Wall
Port, quantity	12

Dimensions

Height	152.4 mm 6 in
Width	228.6 mm 9 in
Depth	101.6 mm 4 in
Cable Length	152.4 m 500 ft

RDT-SJ12J2PC50020

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Indoor
Qualification Standards	NEMA, Type 12

Packaging and Weights

Included	Grommets
Packaging quantity	1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

