

# RDT-SJ12J2PC80020

---

RapidFiber® FDT Distribution Terminal, 12-fiber, SC/APC, 800 ft



## Product Classification

<b>Regional Availability</b>	EMEA   Latin America   North America
<b>Product Type</b>	Fiber distribution terminal
<b>Product Brand</b>	RapidFiber®
<b>Product Series</b>	FDT

## General Specifications

<b>Adapters, quantity</b>	12
<b>Cable Color</b>	Yellow
<b>Cable Entry Location</b>	Bottom left   Top left   Top right
<b>Cable Type</b>	Indoor/outdoor - Stranded
<b>Color</b>	Putty white
<b>Front Cover Type</b>	Hinged with lock
<b>Growth Configuration</b>	Fully loaded
<b>Interface</b>	SC/APC
<b>Interface, stub</b>	No connector
<b>Mounting</b>	Wall
<b>Port, quantity</b>	12

## Dimensions

<b>Height</b>	152.4 mm   6 in
<b>Width</b>	228.6 mm   9 in
<b>Depth</b>	101.6 mm   4 in
<b>Cable Length</b>	243.84 m   800 ft

# RDT-SJ12J2PC80020

---

## Material Specifications

<b>Finish</b>	Powder coated
<b>Material Type</b>	Steel

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
-------------------	------------

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Qualification Standards</b>	NEMA, Type 12

## Packaging and Weights

<b>Included</b>	Grommets
<b>Packaging quantity</b>	1

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant

