1697525 | FD3-AC096J00JKBP2P



FDH 3000 Fiber Distribution Extra Small Pole Mount Cabinet, 72F, SC /APC, O splitters, die. LT, 96F stubs, 100 ft, 24F

Product Classification

Regional Availability North America

Product Type Fiber distribution hub

Product Series FDH 3000

General Specifications

Access Front

Cable TypeDielectric - Loose Tube

Color Putty white

Distribution Cables, quantity

Distribution Ports, quantity 144

Fibers per Distribution Cable, quantity 96

Fibers per Feeder Cable, quantity 24

Interface, Input SC

Interface Feature, Input APC

Mounting Pad

Splitter Slots, quantity 9

Dimensions

Height 914.4 mm | 36 in

Width 533 mm | 20.984 in

 Depth
 355.6 mm | 14 in

 Cable Length
 30.48 m | 100 ft

Enclosure Size Extra small

Material Specifications

Finish Powder coated

Material Type Aluminum

COMMSCOPE®

1697525 | FD3-AC096J00JKBP2P

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

