

# 760237400 | BUDI-S-SEAL-BLIND-PG29

BUDI™ Fiber Optic Cable Sealing Kit for for single cable with a diameter from 15 up to 26mm, no cable fixation



















## Product Classification

<b>Regional Availability</b>	North America
<b>Product Type</b>	Cable sealing
<b>Product Brand</b>	BUDI™
<b>Product Series</b>	BUDI-S

## General Specifications

<b>Application</b>	For holding up to 1 cable with a diameter from 15 up to 26mm, no cable fixation
--------------------	---

## Port Configuration

	BUDI-S-SEAL-4x10	BUDI-M-SEAL-6x10	BUDI-S-SEAL-4x15	BUDI-M-SEAL-6x15	BUDI-S-SEAL-2x20	BUDI-M-SEAL-3x20	BUDI-S-SEAL-24x5	BUDI-M-SEAL-24x5	BUDI-S-SEAL-24x7	BUDI-M-SEAL-24x7	BUDI-S-PTS	BUDI-M-PTS	BUDI-S-SEAL-4x15-MINI-BOT	BUDI-M-SEAL-4x15-MINI-BOT
Max. cable diameter in mm	10	10	15	15	20	20	5	5	7	7	5	5	8.2	8.2
Wrap-around	Y	Y	Y	Y	Y	Y	N	N	N	N	Y	Y	Y	Y
Loop bracket	N	N	N	N	Y	Y	N	N	N	N	N	N	N	N
IP55 (vertical mounting)	Y	Y	Y	Y	Y	Y	Y	Y	Y	Y	N	N	Y	Y
Type of BUDI	 		 		 		 		 		 			

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

