

F3X-J864JJBDDBBB0



FDH 3000 Fiber Distribution Cross-Connect Cabinet, 864F, SC/APC, die. loose tube, 100 ft, 144/216F

Product Classification

Regional Availability	North America
Product Type	Fiber cross-connect hub
Product Series	FDH 3000

General Specifications

Access	Front
Cable Type	Dielectric - Loose Tube
Color	Putty white
Distribution Cables, quantity	5
Distribution Ports, quantity	864
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splitter Slots, quantity	48

Dimensions

Height	1,219.2 mm 48 in
Width	1,168.4 mm 46 in
Depth	558.8 mm 22 in
Cable Length	30.48 m 100 ft
Enclosure Size	Large

Material Specifications

Finish	Powder coated
---------------	---------------

F3X-J864JJBDDBBB0

Material Type Steel

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

