

FD3-MN432J00V00E0B



IFDH 3000 Indoor Fiber Distribution Hub, 432F, SC/APC, loose tube /stranded pigtails, spliced input, 24F feeder

Product Classification

Regional Availability	North America
Product Type	Fiber distribution hub
Product Series	IFDH 3000

General Specifications

Adapters, quantity	432
Cable Type	Pigtails - Stranded
Color	Putty white
Front Door Type	Single hinged
Interface	SC/APC
Mounting	Wall
Port, quantity	432

Material Specifications

Finish	Powder coated
Material Type	Steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Environmental Space	Indoor
----------------------------	--------

Packaging and Weights

Packaging quantity	1
---------------------------	---

FD3-MN432J00V00E0B

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

