# 70191213-02 | 70191213-02



### LSA-PLUS® Comprotect Overvoltage Plug, 2/1, CP HDP GB180C1

Regional Availability	EMEA
Product Type	Overvoltage plug
Product Brand	LSA-PLUS®
General Specifications	
Transmission Standards	DIN EN 60068-2-1   DIN EN 60068-2-2/3   DIN EN 60068-2-6   ITU-T K.12
Dimensions	
Height	12.954 mm   0.51 in
Width	7.874 mm   0.31 in
Length	43.434 mm   1.71 in
Electrical Specifications	
Capacitance	5 pF
Current Rating, maximum	0.12 A
dc Resistance, maximum	1 ohm
Insulation Resistance, minimum	1000 MOhm
Safety Voltage Rating	180 V

### **Environmental Specifications**

Operating Temperature	-20 °C to +60 °C (-4 °F to +140 °F)
Storage Temperature	-40 °C to +80 °C (-40 °F to +176 °F)
Environmental Space	Indoor

Page 1 of 2

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: November 5, 2020



# 70191213-02 | 70191213-02

### Packaging and Weights

Packaging quantity	10
Packaging Type	Bag   Box

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Page 2 of 2

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or <sup>™</sup> are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: November 5, 2020

