760057687 | RFE-HDM-048-6F-SC02

ReadyPATCH® Multimode OM1 Standard High Density Module, 48 SC ports

OBSOLETE

This product was discontinued on: October 16, 2017

Product Classification

Regional Availability	North America
Portfolio	CommScope®
Product Type	Fiber module
Product Brand	OptiSPEED® | ReadyPATCH®

General Specifications

Adapters, quantity, front	24
Adapters, quantity, rear	4
Color, front	Beige
Color, rear	Gray
Data Module Type	Standard
Interface, front	SC
Interface Feature, front	Standard
Interface, rear	MPO Male
Interface Feature, rear	Standard
Shuttered	Yes
Total Fibers, quantity	48
Total Ports, quantity, front	48

Dimensions

Height	32.51 mm | 1.28 in
Width	424.18 mm | 16.7 in
Depth	114.3 mm | 4.5 in

Optical Specifications

Fiber Type	OM1

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 1, 2020

Insertion Loss Change, mating	0.3 dB
Insertion Loss Change, temperature	0.3 dB
Insertion Loss, maximum	1 dB

Environmental Specifications

Safety Standard	UL

Packaging and Weights

Packaging quantity	1

Regulatory Compliance/Certifications

Agency	**Classification**
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss Change, mating	Maximum insertion loss change after 500 matings
Insertion Loss Change, temperature	Maximum insertion loss change from -10 °C to +60 °C (+14 °F to +140 °F)

©2020 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope. All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: September 1, 2020