

NGF-VSP3-00000R



Next Generation Frame (NGF) VAM Block, unloaded, 144-capacity, putty white, right oriented

Product Classification

Regional Availability	EMEA Latin America North America
Product Type	Fiber VAM block
Product Series	NGF

General Specifications

Functionality	Multiplexing Splitting
Application	Used in NGF-style frames only
Body Style	Right orientation
Color	Putty white
Color, front	Putty white
Door Type, front	Compression latch Hinged
Growth Configuration	Fully loaded
Rack Type	NGF
Shelf Movement	Fixed
Total Ports, quantity	144

Dimensions

Height	491.49 mm 19.35 in
Width	182.88 mm 7.2 in
Depth	299.72 mm 11.8 in

Material Specifications

Finish	Powder coated
Material Type	Steel

Environmental Specifications

NGF-VSP3-00000R

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 80%, non-condensing
Qualification Standards	Telcordia GR-449-CORE

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

