

RCP-3J7PUE06100



RapidFiber® Termination Panel, 72-Position 3RU, singlemode, SC/APC to MPO, 61 m

Product Classification

Regional Availability	Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch panel, with rapid cable
Product Brand	RapidFiber®
Product Series	RCP

General Specifications

Functionality	Patching
Body Style	Symmetrical
Cable Exit Location	Rear, left side
Cable Stub Type	Indoor, microcable
Color	Putty white
Door Type, front	Hinged Slide latch Transparent
Growth Configuration	Fully loaded
Interface, front	SC/APC
Interface, rear	MPO
Patch Cord Entry Location	Front, left side Front, right side
Rack Type	EIA 19 in EIA 23 in
Rack Units	3
Shelf Movement	Sliding
Total Fibers, quantity	72
Total Ports, quantity	72
Transmission Standards	IEC 60794-2 ISO/IEC 11801 TIA/EIA-568-B.3


Dimensions

Height	133.35 mm 5.25 in
Width	482.6 mm 19 in

RCP-3J7PUE06100

Depth 381 mm | 15 in
Cable Length 61 m | 200.131 ft

Ordering Tree



Material Specifications

Finish Powder coated
Material Type Steel

Optical Specifications

Fiber Mode Singlemode
Fiber Type G.652.D | G.657.A2/B2

RCP-3J7PUE06100

Environmental Specifications

Operating Temperature	-5 °C to +55 °C (+23 °F to +131 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	5%–85%, non-condensing
Qualification Standards	NEBS Level 3 Telcordia GR-1435 Telcordia GR-326 Telcordia GR-409 UL 1863

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

