RCPB-4CAPUM06100



RapidFiber® Termination Panel, 144-Position LC/UPC to MPO, 4RU, multimode (OM4), 61 m, black

Product Classification

Regional Availability Latin America | North America

Portfolio CommScope®

Product Type Fiber patch panel, with rapid cable

Product Brand RapidFiber®

Product Series RCP

General Specifications

Functionality Patching

Body Style Symmetrical

Cable Exit LocationRear, left side

Cable Stub Type Indoor, microcable

Color Black
Color, front Black

Door Type, front Hinged | Slide latch | Transparant

Growth ConfigurationFully loadedInterface, frontLC/UPCInterface, rearMPO

Patch Cord Entry Location Front, left side | Front, right side

Rack Type EIA 19 in | EIA 23 in

Rack Units 4

Shelf MovementSlidingTotal Fibers, quantity144Total Ports, quantity144

COMMSC PE°

RCPB-4CAPUM06100

Transmission Standards IEC 60794-2 | ISO/IEC 11801 | TIA/EIA-568-B.3

Dimensions


 Height
 177.8 mm | 7 in

 Width
 482.6 mm | 19 in

 Depth
 381 mm | 15 in

 Cable Length
 61 m | 200.131 ft

Ordering Tree



Material Specifications

Finish Powder coated

Material Type Steel

COMMSCOPE®

RCPB-4CAPUM06100

Optical Specifications

Fiber Mode Multimode

Fiber Type OM4, bend insensitive

Environmental Specifications

Operating Temperature $-5 \degree \text{C to } +55 \degree \text{C (} +23 \degree \text{F to } +131 \degree \text{F)}$ Storage Temperature $-40 \degree \text{C to } +70 \degree \text{C (} -40 \degree \text{F to } +158 \degree \text{F)}$

Relative Humidity 5%–85%, non-condensing

Qualification Standards NEBS Level 3 | Telcordia GR-1435 | Telcordia GR-326 | Telcordia GR-409 | UL 1863

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

