

TFP-12MPRFQ2

TFP Fiber Optic Module, MPO, 12-fiber, MPO-LC, Multimode, OM4, right, aqua

OBSOLETE

This product was discontinued on: August 31, 2020

Product Classification

Regional Availability	Asia Latin America North America
Portfolio	CommScope®
Product Type	Fiber module
Product Series	TFP

General Specifications

Functionality	Breakout
Application	For use with TFP panels
Adapter Color	Aqua
Adapters, quantity, front	6
Adapters, quantity, rear	1
Body Style	Duplex Right orientation
Color, front	Black
Color, housing	Black
Color, rear	Black
Interface, front	LC/UPC
Interface, rear	MPO
Interface Feature, rear	Standard
Total Ports, quantity, front	12

Dimensions

Height	33.53 mm 1.32 in
Width	176.02 mm 6.93 in
Depth	143 mm 5.63 in

Optical Specifications

TFP-12MPRFQ2

Fiber Mode	Multimode
Fiber Type	OM4

Environmental Specifications

Operating Temperature	0 °C to +70 °C (+32 °F to +158 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Packaging and Weights

Packaging quantity	1
Packaging Type	Bag Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

