

760202630 | 360-iP-UP-KIT-AE-24



SYSTIMAX 360™ iPatch® Upgrade Kit for Evolve Angled Panel, 24 Port, 10 pack

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

RJ45 patch panel

Product Brand

SYSTIMAX 360™ | iPatch®

General Specifications

ANSI/TIA Category

6 | 6A

Color

Cool gray

Intelligence Type

iPatch® upgrade kit

Panel Style

Angled

Total Ports, quantity

24

Dimensions

Compatible Diameter Over Dielectric, maximum

1.168 mm | 0.046 in

Compatible Diameter Over Dielectric, minimum

0.762 mm | 0.03 in

Electrical Specifications

Current Rating at Temperature

1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface

1,500 Vac @ 60 Hz

Dielectric Withstand Voltage, RMS, contact-to-contact

1,000 Vac @ 60 Hz

Material Specifications

Material Type

Acrylonitrile butadiene styrene (ABS) | Polycarbonate

Environmental Specifications

Operating Temperature

-5 °C to +50 °C (+23 °F to +122 °F)

Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

760202630 | 360-iP-UP-KIT-AE-24

Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	ACMA CE UL cUL

Packaging and Weights

Packaging quantity	10
Weight, net	0.113 kg 0.25 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

