

760238951 | FD-8-1U-A



1RU patch panel which interfaces with QSFP ports to easily break them out in LC connections. The MPO and LC ports are both front facing for easy mapping and patching. 10 singlemode MPO-8 and 40 duplex shuttered LC ports, Method A

Product Classification

| | |
|------------------------------|---|
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |
| Portfolio | CommScope® |
| Product Type | Fiber patch panel |

General Specifications

| | |
|------------------------------|--------------|
| Color | Black |
| Interface, front | LC/UPC MPO |
| Rack Units | 1 |
| Shelf Movement | Fixed |
| Total Ports, quantity | 90 |

Dimensions

| | |
|---------------|--------------------|
| Height | 44.45 mm 1.75 in |
| Width | 482.6 mm 19 in |
| Depth | 292.1 mm 11.5 in |

Optical Specifications

| | |
|--------------------------------|--------|
| Insertion Loss, maximum | 0.6 dB |
|--------------------------------|--------|

Environmental Specifications

| | |
|------------------------|----------|
| Safety Standard | UL 60950 |
|------------------------|----------|

Packaging and Weights

| | |
|---------------------------|---|
| Packaging quantity | 1 |
|---------------------------|---|

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|-----------------------|
|---------------|-----------------------|

760238951 | FD-8-1U-A

| | |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS | Compliant/Exempted |
| UK-ROHS | Compliant/Exempted |

