

760239070 | UDS-6U-BK-LA-A



UDS 6RU splice panel, 432 duplex LC/APC ports, Method A

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Series	UDS

General Specifications

Application	Preloaded with 36 UDS modules
Color	Black
Intelligence Type	Not iPatch® ready
Interface, front	LC/APC
Pigtail Assembly Type	12-fiber, ribbon
Pigtails Included, quantity	72
Rack Type	EIA 19 in
Rack Units	6
Shelf Movement	Fixed
Splice Trays Included, quantity	6
Total Ports, quantity	432

Dimensions

Height	266.7 mm 10.5 in
Width	444.5 mm 17.5 in
Depth	609.6 mm 24 in

Optical Specifications

760239070 | UDS-6U-BK-LA-A

Insertion Loss, maximum 0.4 dB

Environmental Specifications

Safety Standard cUL US 1863

Packaging and Weights

Packaging quantity 1

Weight, net 20.412 kg | 45 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

