

FD3-PA048J00U2220



FDH 3000 Fiber Distribution Hub in a Pedestal, 48F, SC/APC, no splitters, stranded pigtails, 48 splice cap., 12F feeder

- Metal cabinet and can be placed in the ground without pouring a concrete pad or installing a hand hole
- Typically deployed for neighborhoods of 144 homes or higher
- Features full size trays for splicing incoming feeder and outgoing distribution cables and the option of adding hardened drop connections
- Modeled after the FDH 3000 fiber distribution hubs

Product Classification

Regional Availability	North America
Product Type	Hub in a pedestal
Product Series	FDH 3000

General Specifications

Access	Front Rear
Cable Type	Pigtails - Stranded
Color	Green
Distribution Cables, quantity	4
Distribution Ports, quantity	48
Fibers per Distribution Cable, quantity	12
Fibers per Feeder Cable, quantity	12
Interface, Input	SC
Interface Feature, Input	APC
Mounting	Pad
Splice Tray Included, quantity	2
Splice Tray Type Included	24-way, heat shrink
Splicing Capacity, maximum	48
Splitter Slots, quantity	6

Dimensions

Height	889 mm 35 in
Width	292.1 mm 11.5 in

FD3-PA048J00U2220

Depth 368.3 mm | 14.5 in

Enclosure Size Small

Material Specifications

Material Type Steel

Environmental Specifications

Environmental Space Above ground

Packaging and Weights

Packaging quantity 1

Packaging Type Pallet

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

