760237054 | UNP-UDDM-SL-1U-48



Discrete Distribution Module Panel, Cat6, UTP, 1U, 48 port

OBSOLETE

Replaced By:

760237060 CPP-6-UDDM-SL-1U-48

Unshielded Discrete Distribution Module Panel, Cat 6, SL, 1U, 48 port, Black

Product Classification

Regional AvailabilityNorth AmericaPortfolioUniprise®

Product Type RJ45 patch panel

General Specifications

ANSI/TIA Category 6

Cable Type Unshielded

Color Black

Modules, quantity 4

Panel StyleStraightRack TypeEIA 19 in

Rack Units 1

Total Ports, quantity 48

Wiring T568A | T568B

Dimensions

Height44.45 mm| 1.75 inWidth482.6 mm| 19 inDepth, with cable management93.98 mm| 3.7 inCompatible Diameter Over Dielectric, maximum1.168 mm| 0.046 inCompatible Diameter Over Dielectric, minimum0.762 mm| 0.03 in

Page 1 of 2



760237054 | UNP-UDDM-SL-1U-48

Electrical Specifications

Current Rating at Temperature $1.5 \text{ A} \otimes 20 \text{ °C} + 1.5 \text{ A} \otimes 68 \text{ °F}$

Dielectric Withstand Voltage, RMS, conductive surface1,500 Vac @ 60 HzDielectric Withstand Voltage, RMS, contact-to-contact1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Material Specifications

Material Type High-impact, flame retardant, thermoplastic | Powder-

coated steel

Environmental Specifications

Operating Temperature $-10 \,^{\circ}\text{C}$ to $+60 \,^{\circ}\text{C}$ (+14 $^{\circ}\text{F}$ to +140 $^{\circ}\text{F}$)

Storage Temperature $-40 \,^{\circ}\text{C}$ to $+70 \,^{\circ}\text{C}$ (-40 $^{\circ}\text{F}$ to $+158 \,^{\circ}\text{F}$)

Relative HumidityUp to 95%, non-condensing

Flammability Rating UL 94 V-0
Safety Standard UL | cUL

Packaging and Weights

Included Modular jacks (48)

Packaging quantity 1

Regulatory Compliance/Certifications

CHINA-ROHS Below maximum concentration value

Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



Agency

