CX0659-000 | OCM6-SP11WS2-61CI1



OCM6 Fiber Optic Splitter Module, Planar, one 1x32 Splitter, singlemode, SC/APC, symmetrical split ratio, in-line style, 61 cm pigtails

Product Classification

Regional Availability EMEA

PortfolioCommScope®Product TypeSplitter module

Product Series OCM6

General Specifications

Device Type Standard VAM

Functionality Splitting

Technology Type Planar lightwave circuit (PLC)

Application For use with BUDI wall boxes

Circuits, quantity 1

Distribution Type 1 x 32 splitter

Interface, InputSC/APCInterface, OutputSC/APC

Split Ratio Symmetrical

Splitter, quantity 1

Dimensions

 Height
 130 mm | 5.118 in

 Width
 49.8 mm | 1.961 in

 Depth
 16.5 mm | 0.65 in

 Pigtail Length, Output
 0.61 m | 2.001 ft

 Pigtail Diameter
 1.8 mm | 0.071 in



CX0659-000 | OCM6-SP11WS2-61CI1

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

