

EH0776-000 | OCM6-SP218S2-18DB1



OCM6 Fiber Optic Splitter Module, Planar, two 1x8 Splitters, singlemode, SC/APC, symmetrical split ratio, butt style, 1.8 m pigtailed

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Splitter module
Product Series	OCM6

General Specifications

Device Type	Standard VAM
Functionality	Splitting
Technology Type	Planar lightwave circuit (PLC)
Application	For use with BUDI wall boxes
Circuits, quantity	2
Distribution Type	1 x 8 splitter
Interface, Input	SC/APC
Interface, Output	SC/APC
Split Ratio	Symmetrical
Splitter, quantity	2

Dimensions

Height	130 mm 5.118 in
Width	49.8 mm 1.961 in
Depth	16.5 mm 0.65 in
Pigtail Length, Input	1.8 m 5.906 ft
Pigtail Length, Output	1.8 m 5.906 ft
Pigtail Diameter	1.8 mm 0.071 in

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

