

# EK2987-000 | OCM6-SP11WS2-20DB1

---



OCM6 Fiber Optic Splitter Module, Planar, one 1x32 Splitter, singlemode, SC/APC, symmetrical split ratio, butt style, 2 m pigtails

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Splitter module
<b>Product Series</b>	OCM6

## General Specifications

<b>Device Type</b>	Standard VAM
<b>Functionality</b>	Splitting
<b>Technology Type</b>	Planar lightwave circuit (PLC)
<b>Application</b>	For use with BUDI wall boxes
<b>Circuits, quantity</b>	1
<b>Distribution Type</b>	1 x 32 splitter
<b>Interface, Input</b>	SC
<b>Interface Feature, Input</b>	APC
<b>Interface, Output</b>	SC
<b>Interface Feature, Output</b>	APC
<b>Split Ratio</b>	Symmetrical
<b>Splitter, quantity</b>	1

## Dimensions

<b>Height</b>	130 mm   5.118 in
<b>Width</b>	49.8 mm   1.961 in
<b>Depth</b>	16.5 mm   0.65 in
<b>Pigtail Length, Input</b>	2 m   6.562 ft

# EK2987-000 | OCM6-SP11WS2-20DB1

---

**Pigtail Length, Output** 2 m | 6.562 ft  
**Pigtail Diameter** 1.8 mm | 0.071 in

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

### Agency

CHINA-ROHS

REACH-SVHC

ROHS

### Classification

Below maximum concentration value

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

Compliant

