

760065888 | MODG2-12LCA-SM-PT



G2 Modular Cassette with 12 LC APC TeraSPEED® Singlemode Pigtails

OBSOLETE

Replaced By:

760109504
360G2 Cartridge 12-LCA-SM-GR-PIGTAILS 360G2 Singlemode Fiber Cassette 12 LC APC, with pigtails, iPatch Ready

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTMIX®
Product Type	Fiber cassette with pigtails
Product Brand	TeraSPEED®

General Specifications

Adapter Color	Green
Interface, front	LC/APC
Interface, rear	Stranded pigtail
Total Fibers, quantity	12
Total Ports, quantity, front	12

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in
Pigtail Length	1.5 m 4.921 ft

Optical Specifications

Fiber Type	G.652.D and G.657.A1, TeraSPEED® OS2
Insertion Loss, typical	0.4 dB
Return Loss, minimum	65 dB

Environmental Specifications

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

ISO 9001:2015


Classification

Designed, manufactured and/or distributed under this quality management system

Included Products

760066639 - TeraSPEED® LC-APC Multiport Shuttered Adapter, Green, 10 Bulk Pack
AFA-LC12-GR-10-BULK-PACK-SHUTTERED

760066639 | AFA-LC12-GR-10-BULK-PACK-SHUTTERED



TeraSPEED® LC-APC Multiport Shuttered Adapter, Green, 10 Bulk Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	TeraSPEED®
Product Series	AFA

General Specifications

Body Style	Ganged
Color	Green
Interface	LC/APC
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	12

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

760066639 | AFA-LC12-GR-10-BULK-PACK-SHUTTERED

UK-ROHS

Compliant

