760082479 | RK3-45A



Equipment Rack, 2-Post, 3 in (76 mm) Channel x 7ft (2134 mm) H - 19 in (482.6 mm) Alu (45U) 12-24 Tapped Rails, Black

Product Classification

Regional Availability Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

Product Type 2 post rack

General Specifications

Color Black

Rack Type EIA 19 in

Rack Units 45

Rail Mounting Hole #12-24

Dimensions

Height 2,133.6 mm | 84 in

Channel Width 76.2 mm | 3 in

Width 518.16 mm | 20.4 in

Depth 381 mm | 15 in

Dimensional Standards EIA-310-E

Material Specifications

Finish Powder-coated, textured

Material Type Aluminum

Mechanical Specifications

Static Load Rating 453.6 kg | 1,000.016 lb

Packaging and Weights

Included Forty #12-24 x 1/2 in mounting screws | Instruction sheet | Twelve 3/8 in split lock

washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base

Page 1 of 2

760082479 | RK3-45A

angles | Two extruded top angles | Two vertical rack rails

Packaging quantity

Packaging Type Flat packed

Weight, net 12.7 kg | 27.999 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant



