760090167 | RK12-52S



Equipment Rack, 2-Post, 12 in (305 mm) Channel x 8ft (2438 mm) H - 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	2 post rack

General Specifications

Color	Black
Rack Type	EIA 19 in
Rack Units	52
Rail Mounting Hole	3/8 in

Dimensions

Height	2,438.4 mm 96 in
Channel Width	304.8 mm 12 in
Width	518.16 mm 20.4 in
Depth	609.6 mm 24 in
Dimensional Standards	EIA-310-E

Material Specifications

Finish	Powder-coated, textured

Steel

Material Type

Mechanical Specifications

Static Load Rating 453.6 kg | 1,000.016 lb

Packaging and Weights

Included

Forty M6 cage nuts | Forty M6 x 12 mm mounting screws | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 15, 2023



760090167 | RK12-52S

Packaging quantity	1
Packaging Type	Flat packed
Weight, net	28.12 kg 61.994 lb

Regulatory Compliance/Certifications

Agency

ISO 9001:2015



Classification Designed, manufactured and/or distributed under this quality management system

base angles | Two extruded top angles | Two vertical rack rails



©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: August 15, 2023

