## 760109579 | 360G2 Cartridge 6-SCA-SM-GR-PIGTAILS A



360G2 Singlemode Fiber Cassette 6 SC APC with pigtails A

## **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio CommScope®

**Product Type** Fiber cassette with pigtails

Product Series G2

General Specifications

Color, front Green

Intelligence Type Not iPatch® ready

Interface, front SC/APC

Interface, rear Stranded pigtail

**Total Ports, quantity, front** 6

Dimensions

 Height
 25.908 mm | 1.02 in

 Width
 94.996 mm | 3.74 in

 Depth
 123.012 mm | 4.843 in

Optical Specifications

Fiber ModeSinglemodeFiber TypeG.657.A1Insertion Loss, maximum0.58 dB

**Environmental Specifications** 

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

Page 1 of 2

## 760109579 | 360G2 Cartridge 6-SCA-SM-GR-PIGTAILS A

Safety Standard CE | CSA | UL

Packaging and Weights

Packaging quantity

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted

