



Shielded Angled Discrete Distribution Module Panel, SL, 2U, 48 port, Black

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	RJ45 patch panel
Product Series	SLX Series

General Specifications

Cable Type	Shielded
Color	Black
Modules, quantity	0
Panel Style	Angled
Rack Type	EIA 19 in
Rack Units	2
Total Ports, quantity	48

Dimensions

Height	88.9 mm 3.5 in
Width	482.6 mm 19 in
Depth, with cable management	210.82 mm 8.3 in

Material Specifications

Material Type	High-impact, flame retardant, thermoplastic Powder-coated steel
----------------------	---

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Flammability Rating	UL 94 V-0

760237049 | CPPA-SDDM-SL-2U-48

Safety Standard RCM | UL | cUL

Packaging and Weights

Packaging Material Eco-friendly, single-use plastics-free

Packaging quantity 1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

