



G2 Splice Cassette, 24LC, no pigtails

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber cassette
Product Series	G2

General Specifications

Color, front	Aqua Blue Green Lime green
Interface, front	LC/UPC
Interface, rear	No pigtail
Shuttered	Yes
Total Fibers, quantity	24

Dimensions

Height	26.416 mm 1.04 in
Width	96.52 mm 3.8 in
Depth	165.354 mm 6.51 in

Material Specifications

Alignment Sleeve Material	Zirconia
----------------------------------	----------

Environmental Specifications

Qualification Standards	IEC 61753-1 TIA-568.3-D
Safety Standard	UL

Packaging and Weights

Included	Colored faceplates SMOUV holder SMOUV splice protection
Packaging quantity	1

Weight, net 0.107 kg | 0.235 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

