

EG8357-000 | FIST-GPS2-72-S2-AD

FIST-GPS2 Fiber Termination/Splice Panel, 72 SC/APC, 19 in, gray

Product Classification

Regional Availability	EMEA
Portfolio	CommScope®
Product Type	Fiber patch/splice panel
Product Brand	FIST®
Product Series	FIST-GPS2

General Specifications

Functionality	Patching Splicing
Application	Used in FIST-GR3-style frames only
Color	Gray
Color, front	Gray
Interface, front	SC/APC
Rack Type	EIA 19 in ETSI 600 mm
Rack Units	3
Shelf Movement	Sliding
Total Ports, quantity	72

Dimensions

Width	482.6 mm 19 in
--------------	------------------

Material Specifications

Finish	Powder coated
Material Type	Galvanized steel

Optical Specifications

Fiber Mode	Singlemode
-------------------	------------

Environmental Specifications

Operating Temperature	-5 °C to +45 °C (+23 °F to +113 °F)
Storage Temperature	-30 °C to +60 °C (-22 °F to +140 °F)

EG8357-000 | FIST-GPS2-72-S2-AD

Relative Humidity Up to 93%, non-condensing

Packaging and Weights

Included Mounting hardware

Packaging quantity 1

Regulatory Compliance/Certifications

Agency

Classification

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

