



PEDCAP Copper Closure, butt, unpressurized, heat shrink, 120 mm joint length, for up to 4 cables

- One piece end cap with heat-shrinkable outlet for sealing onto the cables
- Provides an excellent environmental and mechanical seal for telephone splices in the distribution network
- Suitable for use as an overhead, underground or pedestal joint closure in both new construction and maintenance applications

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Unpressurized heat shrink closure
Product Series	PEDCAP

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Cable Capacity, maximum	4
Cable Sealing Type	Hotmelt adhesive
Closure Style	Single-ended
Color	Black
Mounting	Pedestal
Splicing Capacity, maximum	200

Dimensions

Length	330 mm 12.992 in
Single Cable Diameter, maximum	40 mm 1.575 in
Single Cable Diameter, minimum	11 mm 0.433 in
Splice Bundle Diameter, maximum	57 mm 2.244 in
Sheath Opening, nominal	120 mm 4.724 in

Material Specifications

075888-000 | PED-CAP-R-3-INT

Material Type Polyolefin

Environmental Specifications

Environmental Space Aerial | Buried

Packaging and Weights

Included Aluminum closing strip | Aluminum foil | Cleaning tissues | Desiccant | Tie wraps

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

