# 142995-000 | XAGA-1000-200/65-720A340



XAGA® 1000 Copper Closure, pressurized, heat shrink, 720 mm sheath opening, 200 mm splice bundle diameter

- High performance heat-shrinkable closure for both maintenance and new constructions
- Suitable for use with all standard copper connector systems
- Full range of closures to suit all copper cable sizes

#### OBSOLETE

This product was discontinued on: June 30, 2022

#### Product Classification

Regional Availability	EMEA
Product Type	Pressurized heat shrink closure
Product Brand	XAGA®
Product Series	XAGA 1000
General Specifications	
Application	For use with Polyethylene and metal jacketed cables
Branch-off Clip	To be ordered seperately
Cable Capacity, maximum	4
Cable Sealing Type	Hotmelt adhesive
Closure Style	In-line
Color	Black
Mounting	Duct   Manhole
Splice Protection Type	Metal canister with valve

#### Dimensions


Single Cable Diameter, minimum	65 mm   2.559 in
Splice Bundle Diameter, maximum	200 mm   7.874 in
Sheath Opening, nominal	720 mm   28.346 in

## Dimension Drawing

Page 1 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023

**COMMSCOPE**<sup>®</sup>



# Material Specifications

Material Type

Fiber-reinforced multi-layer sealing sleeve

## **Environmental Specifications**

Environmental Space	Aerial   Below ground   Buried
Packaging and Weights	
Included	Abrasive strip   Aluminum closing strip   Aluminum foil   Cleaning tissues   Flexible stainless steel channels   Heatshrinkable sleeve   Metal canister   Shield continuity wire   Underclips   Valve hardware
Packaging quantity	1
Packaging Type	Bag   Carton

#### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant



Page 2 of 2

©2023 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: March 20, 2023

**COMMSCOPE**°