

TTRC Copper Closure, unpressurized, gel sealed, 260 mm sheath opening, for up to 25 pair splices



- Watertight, toolless, torchless and re-usable closure for aerial applications
- Seals unpressurised inline splices in new construction and network maintenance applications up to 600 pairs
- Sealing on both the closure body and a multiple of cables is performed by compressing the gel material between two plastic flanges
- Gel compression is activated by a built-in tensioning mechanism

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Gel sealed closure
<b>Product Series</b>	TTRC

## General Specifications

<b>Application</b>	For use with Polyethylene cables
<b>Cable Capacity, maximum</b>	4
<b>Cable Sealing Type</b>	Gel filled
<b>Closure Style</b>	In-line
<b>Color</b>	Black
<b>Mounting</b>	Strand
<b>Splicing Capacity, maximum</b>	25

## Dimensions

<b>Single Cable Diameter, maximum</b>	19 mm   0.748 in
<b>Single Cable Diameter, minimum</b>	10 mm   0.394 in
<b>Splice Bundle Diameter, maximum</b>	72 mm   2.835 in
<b>Sheath Opening, nominal</b>	260 mm   10.236 in

