



RABC Copper Closure, butt, unpressurized, heat shrink, 580 mm joint length, for up to 4 cables

- Suitable for use as an overhead, underground or pedestal joint closure in both new construction and maintenance applications
- Provides an excellent environmental and mechanical seal for telephone splices in the distribution network

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability	EMEA
Product Type	Unpressurized heat shrink closure
Product Series	RABC

General Specifications

Application	For use with Polyethylene and metal jacketed cables
Cable Capacity, maximum	4
Cable Sealing Type	Hotmelt adhesive
Closure Style	Single-ended
Color	Black

Dimensions

Length	800 mm 31.496 in
Single Cable Diameter, maximum	155 mm 6.102 in
Single Cable Diameter, minimum	60 mm 2.362 in
Splice Bundle Diameter, maximum	135 mm 5.315 in
Sheath Opening, nominal	580 mm 22.835 in

Material Specifications

Material Type	Polyolefin
----------------------	------------

Environmental Specifications

Environmental Space Aerial | Buried

Packaging and Weights

Included Abrasive strip | Aluminum foil | Branch-off clip | Clamp | O-ring seal | Tie wraps

Packaging quantity 1

Packaging Type Bag | Carton

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

