

# 760175711 | RK-4PE-52-29S



Equipment Rack, 4-Post, 29 in (737 mm) D x 8 ft (2438 mm) H - 19 in (482.6 mm) Steel (52U) 3/8 Sq Punch, Black

## OBSOLETE

### Replaced By:

760175703  
RK-4PE-45-29S

Equipment Rack, 4-Post, 29 in (737 mm) D x 7 ft (2134 mm) H - 19 in (482.6 mm) Steel (45U) 3/8 Sq Punch, Black

## Product Classification

|                              |   |
|------------------------------|---|
| <b>Regional Availability</b> | Asia   Australia/New Zealand   EMEA   Latin America   North America |
| <b>Portfolio</b>             | CommScope®  |
| <b>Product Type</b>          | 4 post rack   |

## General Specifications

|                           |           |
|---------------------------|-----------|
| <b>Color</b>              | Black     |
| <b>Rack Type</b>          | EIA 19 in |
| <b>Rack Units</b>         | 52        |
| <b>Rail Mounting Hole</b> | 3/8 in    |

## Dimensions

|                              |                     |
|------------------------------|---------------------|
| <b>Height</b>                | 2,438.4 mm   96 in  |
| <b>Width</b>                 | 518.16 mm   20.4 in |
| <b>Depth</b>                 | 1,041.4 mm   41 in  |
| <b>Dimensional Standards</b> | EIA-310-E           |

## Material Specifications

|                      |                         |
|----------------------|-------------------------|
| <b>Finish</b>        | Powder-coated, textured |
| <b>Material Type</b> | Steel                   |

## Mechanical Specifications

|                    |                      |
|--------------------|----------------------|
| <b>Load Rating</b> | 907.185 kg   2000 lb |
|--------------------|----------------------|

## Environmental Specifications

**Safety Standard** UL | cUL

## Packaging and Weights

**Included** Base pan | Forty #12-24 x 1/2 in mounting screws | Forty M6 cage nuts | Four vertical rack rails | Instruction sheet | Twelve 3/8 in split lock washers | Twelve 3/8-16 UNC x 1 in hex head bolts | Twelve 3/8-16 hex nuts | Two extruded base angles | Two extruded top angles | Upper plate support

**Packaging quantity** 1

**Packaging Type** Flat packed

**Weight, net** 52.16 kg | 114.993 lb

## Regulatory Compliance/Certifications

| Agency        | Classification   |
|---------------|--|
| CHINA-ROHS    | Below maximum concentration value  |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system   |
| REACH-SVHC    | Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a> |
| ROHS          | Compliant  |
| UK-ROHS       | Compliant  |

