


# 760238936 | EHD-SP-24LC-SM-B-ULL



EHD ULL Singlemode Splice Cassette, 24LC with dust plugs and pigtails

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Product Brand</b>	SYSTIMAX ULL
<b>Product Series</b>	EHD

## General Specifications

<b>Color, front</b>	Blue
<b>Interface, front</b>	LC/UPC
<b>Interface, rear</b>	Stranded pigtail
<b>Polarity</b>	Method B Enhanced
<b>Shuttered</b>	No
<b>Total Fibers, quantity</b>	24

## Dimensions

<b>Height</b>	11.43 mm   0.45 in
<b>Width</b>	169.672 mm   6.68 in
<b>Depth</b>	163.83 mm   6.45 in

## Optical Specifications

<b>Fiber Mode</b>	Singlemode
<b>Fiber Type</b>	G.657.A2
<b>Insertion Loss, maximum</b>	0.25 dB

# 760238936 | EHD-SP-24LC-SM-B-ULL

---

## Environmental Specifications

**Qualification Standards** IEC 61753-1 | TIA-568.3-D

**Safety Standard** CE | CSA | UL

## Packaging and Weights

**Included** Single Fusion Splice Protection Sleeves

**Packaging quantity** 1

**Weight, net** 0.181 kg | 0.4 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted



## Included Products

- FST-ACC005 – Fiber Optic Protective Splice Sleeve, 1 package

# FST-ACC005

---



Fiber Optic Protective Splice Sleeve, 1 package

## Product Classification

**Regional Availability** North America  
**Product Type** Fiber protection sleeve

## General Specifications

**Splicing Type** Heat shrink, single fiber fusion

## Environmental Specifications

**Storage Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

## Packaging and Weights

**Packaging quantity** 1

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

