

Rack 19" 24 HU 800x800 perforated

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Product Type Network cabinet, with perforated doors

General Specifications

Color Gray

Mounting M6 Cage nut rail mounting

Note Static load rating is 1000 kg

Rack Type EIA 19 in

Dimensions

Height 1200 mm | 47.244 in

Height, guide rails 1,066.8 mm | 42 in

Width 800 mm | 31.496 in

Depth 800 mm | 31.496 in

Electrical Specifications

Electrical Safety Standard UL | cUL

Voltage Range On-site configuration dependant

Material Specifications

Material Type Galvanized sheet metal | Powder-coated, textured

Packaging and Weights

Height, packed 1400 mm | 55.118 in

Width, packed 960 mm | 37.795 in

Depth, packed 1222 mm | 48.11 in

Included Cables ducts (2) | Cage nuts M6 (30) | Grounding cables (10) | Grounding rail (1) | Guide rails (16) | Raised head screws M6 (30)

7712942-00

Packaging quantity	1
Weight, gross	145 kg 319.67 lb
Weight, net	82 kg 180.779 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

